



CONNECTIONS YOU CAN RELY ON

NEW FOR 2015




PHARMACEUTICAL DRY LINK®

Dry Link®



- Internals polished to 20 RA micro-inch mirror finish
- The only true drip-free coupling on the market
- Externals can be polished and are suitable for cleanroom applications
- Available in sizes ¼" through to 4"




Across small scale labs, medium sized batch processors and large scale manufacturers, our sanitary Dry Link couplings will suit your needs. These polished couplings are the only true sanitary drip-free couplings available, due to their simple butterfly design.

We offer both wetted internal components polished to 20 RA micro inch finish, or unpolished internals at an economy price. The smooth mirror polished bore has no voids, crevices or fillers that could trap bacteria, the external parts of the coupling can be polished to a high level and have been accepted in clean room applications.

APPLICATIONS

For the safe and secure transfer of toxic materials in the pharmaceutical, biotech, cosmetic and food manufacturing process.

- 
- Competitively priced
 - Ultra safe design, minimising risk of spillage
 - Handles automatically lock into the body for ease of use
 - Can be connected to any standard cam adaptor

ECO-LOK™



The self-locking ECO-LOK™ offers all the convenient ease and multiple uses of a standard cam and groove coupling, with the addition of a safety locking arm. Such a design ensures that the arms are locked automatically when closed, making it an excellent choice for the transfer of expensive or hazardous materials. To open, simply pull the finger ring down and the handle will open in the normal way.


APPLICATIONS

Specifically for liquid chemicals and pharmaceuticals but also for cosmetics, foodstuffs, inks, adhesives and dyes - particularly where safety and costs are important.

AZURE® ADBLUE SPILL PREVENTION ADAPTOR



Your Dry Break adaptor for
AdBlue
Transfers



AZURE®

Now that over half the trucks on the roads are using AdBlue and rising everyday, it has never been so important to use a dedicated adaptor in your AdBlue fluid transfer system. The new Azure® adaptor from Action-Sealtite Ltd has been specifically designed to eliminate spillage and environmental contamination, waving goodbye to expensive catalyst replacement costs further down the line.

The Azure® tank unit is designed to connect with our CleanBREAK™ and other dry break hose units.

- Market leading price
- Branded with the QuickBreak® name
- Multi-purpose
- Interchangeable with Hansen / Faster / Perfecting / Rectus series

QUICKBREAK® QUICK DISCONNECTS




Consisting of couplings designed to ISO 7241-A (ISO A) and ISO 7241-B (ISO B) parts, the QuickBreak® multi-purpose poppet couplings are branded with the product code, material and size for track and traceability. Upon disconnection, the socket and plug valves seal instantly, automatically shutting off fluid flow to prevent leakage. On connection, the socket and plug valve push together, opening to permit free flow of fluid.

APPLICATIONS

High pressure hydraulic circuits, connection of hydraulic pumps, valves and quick tool change, aluminium die casting, test benches, plastic industry tool changing and steel industry.

CHEMICAL PUMPS

Ask us about our range of **chemical pumps...** We have the pump to help your application



- Diaphragm pumps
- Centrifugal pumps
- Progressive cavity pumps
- Gear pumps
- Air operated pumps
- Multistage pumps
- Vertical inline pumps
- Split casing pumps
- Barrel pumps
- Vertical immersion pumps

Need a **flow meter** to measure and monitor your fluid transfer system? We will offer the right flow meter for your application

FLOW METERS

- Water flow meters
- Turbine flow meters
- Oil flow meters
- Gas flow meters
- Electricity flow meters
- Steam flow meters
- Heat flow meters
- Chemical flow meters
- Ultrasonic flow meters



With over 30 years experience within the fluid transfer sector, it's easy to see why people approach Action-Sealtite Ltd for their camlock couplings, dry disconnects and flexible hose needs. As we continue to launch new and exciting products into the market place, we invite you to get in touch with our technical advisors for more information and prices.

In our 2014 Customer Survey, we learnt:

Over 95% of our customers rated our range of products good or excellent.

96% of our customers rated our Product Quality & Reliability as good or excellent.

Over 87% of our customers rated our Prices/Value for Money as good or excellent.

To find out how our products and services can help you, get in contact:

Tel: +44 (0)1235 512 500
Fax: +44 (0)1235 512 666
Email: sales@actionsealtite.com
Web: www.actionsealtite.com

